





Dimensional drawings

Flush-mounting distribution boards



Device mounting depth 55 mm (left) and 70 mm (right)



Hollow-wall distribution boards



Device mounting depth 55 mm (dimensions in parentheses apply to mounting depths of up to 70 mm)

- 1) Board thickness.
- 2) Minimum clearance 1-row 290 mm, 2-row 415 mm, 3-row 560 mm, 4-row 685 mm
- 3) Required clearance for swinging out the fixing claws.

Surface-mounting distribution boards




Device mounting depth 55 mm (left) and 70 mm (right)

ALPHA Small Distribution Boards



SIMBOX 63

Dimensional drawings




Mounting dimensions



Hood-type distribution boards with door



Hood-type distribution boards without door



Transparent door, snap-in (top) and sealable (bottom)